

Dial Reading Viscometer

our original...over 75 years!

The Worldwide Standard
Viscometer

Easy-to-Select Speeds

Electronic Drive
means quiet,
reliable operation

Analog display
- Shows % Torque
- Use Factor Finder
to convert reading
to centipoise

Simple-to-use,
easy setup

2-Year Limited Warranty

Available in explosion proof
U.L. Class 1, Division 1,
Group D locations
(w/o Electronic Drive)

Accuracy: $\pm 1.0\%$ of range

Repeatability: $\pm 0.2\%$



What's Included?

Instrument

6 spindles (RV/HA/HB) (p45)

or 4 spindles (LV) (p45)

Spindle Guard Leg*

Lab Stand (Model A) (p50)

Carrying Case

*Not applicable to HA or HB torque models

Optional Accessories

Viscosity Standards (p52)

RV/HA/HB-1 Spindle (p45)

Quick Action Lab Stand (p50)

Temperature Bath (p33-35)

Small Sample Adapter (p38)

UL Adapter (p40)

Thermosel (p36)

Helipath Stand with T-bar Spindles (p42)

Spiral Adapter (p44)

DIN Adapter (p44)

Quick Connect/Extension Links (p49)

Vane Spindles (p43 & 48)

MODEL	VISCOSITY RANGE cP(mPa•s)		SPEEDS	
	Min.	Max.	RPM	Number of Increments
LVT	1†	2M	.3-60	8
RVT	100††	8M	.5-100	10
HAT	200††	16M	.5-100	10
HBT	800††	64M	.5-100	10

† 1 cP achieved with UL Adapter accessory. 15 cP on LV with standard spindles.

†† Minimum viscosity is achieved with optional RV/HA/HB-1 spindle.

M = 1 million cP = Centipoise mPa•s = Millipascal•seconds



*Easy Speed
Adjustment
and On/Off
Control*



HOYU

和裕科技 TEL: +886 2 22369391

www.hoyutech.com.tw FAX: +886 2 22369697